



SL-3450

Mini Stage Laser Light with Battery

User Manual

GENERAL INSTRUCTIONS

Thank you for purchasing this product. Please read this user guide for safety and operation information before using this product. This manual contains important information about the safe operation of the SL3450 unit. Keep this manual for future reference. In case of sale of equipment to another user, it is important that this manual is attached to the equipment so that the new user has the necessary information to use and can read the warnings on safe operation.

This product is suitable for creating high-quality laser effects, it can operate for between 4-6 hours continuously via the in built battery. Alternately the unit can use the supplied AC240V power supply to run off mains power.

This unit is designed to produce decorative effect lighting for home and recreational use.

This product is a so-called show laser emitting radiation with a wavelength spectrum and producing lasers for shows. Please refer to the safety instructions specific for lasers.

Before first use, unpack the set and make sure there was no damage during transport. The below parts are supplied with the SL3450:

- 1x Mini Stage Laser Light
- 1 x Adaptor
- 1 x tripod
- 1 x User Manual

SAFETY INSTRUCTIONS

Before using, please be assured that the voltage to be used is appropriate with the information mentioned at the rear panel of the unit. To avoid any shock hazards, do not open or remove the cover.

This unit is designed for indoor use. Do not expose the unit to rain or moisture.

The working temperature of the unit is from 18 to 35°C. Do not use it at higher temperature.

Aim to not use the unit for more than a 4 Hour duration in order to preserve the long term life of the product.

Always unplug the unit when we do not in use it for a long period of time.

Do not place metal objects or spilt liquids in or over the unit. If this occurs, please disconnect the unit from the mains at once.

Keep the device away from flammable or hot sources.

The unit should be placed in a well ventilated area and fixed at least 50 cm at least from the walls.

Do not cover the ventilation openings as it may result in overheating.

Do not use the unit in a dusty environment. Please use a soft cloth to remove dust that has settle on the external lens.

Keep away from children.

Make sure that the area below the setup of the unit is free from unwanted persons.

Do not remove the stickers placed on the unit. It is forbidden to make any unauthorized modifications to the unit due to safety reasons.

If some parts are visibly damaged (power cord, lens, plug, casing brackets), please do not use the unit and contact your dealer

The unit does not have user serviceable parts inside.

Refer to qualified persons or contact your dealer.

Never repair a fuse or bypass the fuse holder.

Please use the original packaging for transporting the

device.

In the event of serious problems, stop using the device and contact your dealer. Do not open the cover.

Never look at the light source directly! Do not use the unit effects in the presence of persons suffering from epilepsy.

Please Note:

Laser lighting is different from any other light sources with which you may be familiar. The light from this product can potentially cause eye injury if not set up and used properly.


Laser light is thousands of times more concentrated than light from other kinds of light source. This concentration can cause eye injuries, through the burning of the retina. Even if you can not feel heat from a laser beam, it can still injure or blind you or the audience.

Never look directly at the laser aperture or laser beams.

SPECIFICATIONS

Power Input:	AC 100-240V, 50/60Hz
Output:	5.0V 1A.
Laser Power:	Green color Wavelength 532nm, Power 50mW; Red color Wavelength 650nm, Power 110mW.
Dimension:	110 x 63 x 42mm
Weight:	0.38KG
Battery Power:	2800mAh
Battery Runtime:	4-6hours;
Battery Charge Time:	6-8hours
Laser Class:	Class 3R laser product

DIAGRAMS



1. MIC
2. Power Switch
3. Laser aperture
4. Power connector

DISTRIBUTED BY:
TechBrands by Electus Distribution Pty. Ltd.
320 Victoria Rd, Rydalmere
NSW 2116 Australia
Ph: 1300 738 555
Int'l: +61 2 8832 3200
Fax: 1300 738 500
www.techbrands.com
Made in China